

# Axis controller SPC200/P05

Part number: 187813

FESTO

For up to 4 pneumatic axes, with PROFIBUS DP connection.



## Data sheet

Feature	Value
Device setup	Basic unit for 4 plug-in modules Power supply Serial interface Subcontroller PROFIBUS interface
CE mark (see declaration of conformity)	to EU directive for EMC
Continuous shock resistance per DIN/IEC 68, parts 2 - 82	Tested in accordance with severity level 2
Relative air humidity	0 - 95 % non-condensing
Protection class	IP20 to IEC 60529
Vibration resistance per DIN/IEC 68, parts 2 - 6	Tested in accordance with severity level 1
Ambient temperature	-5 ... 50 °C