

# Cable socket ASI-SD-PG-M12

Part number: 18789

FESTO



## Data sheet

Feature	Value
Type of mounting	Via union nut
Mounting position	optional
Product weight	27.6 g
Electrical connection	4-pin Straight socket Screw terminal
Operational voltage range AC	125 V
Permissible current load	3 A
Cable fitting	Pg 9
Connection cross section	0.75 mm <sup>2</sup>
Degree of protection	IP65 IP67
Ambient temperature	-40 °C...85 °C
LABS (PWIS) conformity	VDMA24364-B2-L
Note on materials	RoHS-compliant
Material housing	PA
Housing colour	Black
Material union nut	Nickel-plated
Material electrical contact	Bronze