

**CPV10-EPL-EU**

End plate

Data sheet

Part no.: 188454

Page:1

<b>Feature</b>	<b>Data/description</b>
Air connection type	<b>Sub-base</b>
Operating pressure min.	<b>0 bar</b>
Operating pressure max.	<b>10 bar</b>
Minimum ambient temperature	<b>-5 °C</b>
Maximum ambient temperature	<b>50 °C</b>
Sound pressure level	<b>76 dB(A)</b>
Standard nominal flow rate	<b>6400 l/min</b>
Material of shock absorber insert	<b>PE</b>