

QSL-CM-3/8-6**Push-in/threaded L-fitting**

Feature	Data/description
Design structure	Push/pull principle
Ambient temperature	0 - 40 °C
Pneumatic connection	Male thread R3/8 for tubing, 6mm outside diameter
Operating pressure	-0,950 - 6,000 bar
Medium temperature	0,0 - 40,0 °C
Operating medium	Filtered compressed air Vacuum
Nominal size	4,600 mm
Size	Standard
Corrosion resistance classification CRC	1
Type of seal on screw-in stud	coating
Surface resistance	0,010 - 10,000 MOhm
Materials note	Antistatic
Max. tightening torque	22,000 Nm
Materials information, housing	PBT-reinforced