

# Suction cup complete holder ESH-HA-3-QS

Part number: 189197

FESTO



## Data sheet

Feature	Value
Volume	0.52 cm <sup>3</sup>
Mounting position	Vertical
Design	Vacuum port on top
Correlation to suction-cup holder	Size 3
Operating medium	Atmospheric air based on ISO 8573-1:2010 [7::-]
Corrosion resistance class CRC	1 - Low corrosion stress
LABS (PWIS) conformity	VDMA24364-A1-L
Ambient temperature	0 °C...60 °C
Product weight	20 g
Type of mounting	Via lock nut
Suction cup mounting	M4
Vacuum connection	QS-6
Note on materials	RoHS-compliant
Material seals	NBR
Material retaining bracket	Aluminium Nickel-plated brass POM Tempered steel High-alloy steel