

suction cup holder ESH-HCL-3-QS

Part number: 189227

FESTO

with increased height compensator, vacuum connection at top,
compensator secured by two hexagonal nuts.



Data sheet

Feature	Value
Height compensator for suction-cup holder	20 mm
Volume	1.616 cm ³
Assembly position	Vertical
Design structure	Vacuum connection at top with height compensation
Correlation to suction-cup holder	Size 3
Operating medium	Atmospheric air based on ISO 8573-1:2010 [7:-:-]
Corrosion resistance classification CRC	1 - Low corrosion stress
PWIS conformity	VDMA24364-A1-L
Ambient temperature	0 ... 60 °C
Product weight	48 g
Mounting type	with lock nut
suction cup mounting	M4
Vacuum connection	QS-6
Materials note	Conforms to RoHS
Material seals	NBR Steel
Material bracket	Aluminium Nickel-plated brass POM Heat-treatment steel High alloy steel