

Suction cup complete holder ESH-HDL-3-QS

Part number: 189247

FESTO



Data sheet

| Feature | Value |
|---|---|
| Height compensator for suction-cup holder | 20 mm |
| Volume | 0.474 cm ³ |
| Mounting position | Vertical |
| Design | Vacuum port on side With height compensator |
| Correlation to suction-cup holder | Size 3 |
| Operating medium | Atmospheric air based on ISO 8573-1:2010 [7::-] |
| Corrosion resistance class CRC | 1 - Low corrosion stress |
| LABS (PWIS) conformity | VDMA24364-A1-L |
| Ambient temperature | 0 °C...60 °C |
| Product weight | 65 g |
| Type of mounting | Via lock nut |
| Suction cup mounting | M4 |
| Vacuum connection | QS-6 |
| Note on materials | RoHS-compliant |
| Material seals | NBR Steel |
| Material retaining bracket | Aluminium Nickel-plated brass POM Tempered steel High-alloy steel |