

# Suction cup complete holder ESH-HE-1-M3

Part number: 189253

FESTO



## Data sheet

Feature	Value
Nominal size	1.2 mm
Volume	0.04 cm <sup>3</sup>
Mounting position	Vertical
Design	Vacuum port on top
Correlation to suction-cup holder	Size 1
Operating medium	Atmospheric air based on ISO 8573-1:2010 [7::-]
Corrosion resistance class CRC	1 - Low corrosion stress
LABS (PWIS) conformity	VDMA24364-A1-L
Ambient temperature	-10 °C...60 °C
Product weight	1 g
Type of mounting	Via male thread Via vacuum port
Suction cup mounting	Diameter 3 mm
Vacuum connection	M3
Note on materials	RoHS-compliant
Material seals	Wrought aluminium alloy NBR POM Steel
Material retaining bracket	Tempered steel