

Semi-rotary drive DRE-2-F04-Q06-FS-PS

Part number: 189917

FESTO

Single-acting, air connection as per VDI/VDE 3845, Namur valves can be directly flange-mounted

This product is only available if ordered from the Festo Corporation, USA.



Data sheet

Feature	Value
Size of actuator	2
Flange hole pattern	F04
Swivel angle	90 deg
Fitting connection conforms to standard	ISO 5211
Cushioning	No cushioning
Assembly position	Any
Mode of operation	single-acting
Design structure	Rack and pinion
Position detection	No
Valve connection conforms to standard	VDI/VDE 3845 (NAMUR)
Operating pressure	2 ... 10 bar
Operating medium	Compressed air in accordance with ISO8573-1:2010 [7:4:4]
Note on operating and pilot medium	Lubricated operation possible (subsequently required for further operation)
Corrosion resistance classification CRC	3
Ambient temperature	-20 ... 80 °C
Air consumption at 6 bar per cycle 0°-90°-0°	1.2 l
Product weight	600 g
Shaft connection	V11
Pneumatic connection	Sub-base G1/8
Materials note	Contains PWIS substances
Materials information for drive shaft	Aluminium Anodised
Materials information for cover	PA
Materials information for seals	NBR
Materials information, housing	Aluminium Anodised