

# Semi-rotary drive DRE-8-F05-Q10-FO-C

Part number: 190054

FESTO

Single-acting, air connection as per VDI/VDE 3845, Namur valves can be directly flange-mounted



## Data sheet

Feature	Value
Size of actuator	8
Flange hole pattern	F05
Swivel angle	90 deg
Fitting connection conforms to standard	ISO 5211
Cushioning	No cushioning
Assembly position	Any
Mode of operation	single-acting
Design structure	Rack and pinion
Position detection	No
Closing direction	Spring force, opening
Valve connection conforms to standard	VDI/VDE 3845 (NAMUR)
Operating pressure	2 ... 10 bar
ATEX category Gas	II 2G
Explosion ignition protection type Gas	c T6
ATEX category Dust	II 2D
Explosion ignition protection type Dust	c 60°C
Explosion-proof ambient temperature	-20°C ≤ Ta ≤ +60°C
Operating medium	Compressed air in accordance with ISO8573-1:2010 [7:4:4]
Note on operating and pilot medium	Lubricated operation possible (subsequently required for further operation)
CE mark (see declaration of conformity)	to EU directive explosion protection (ATEX)
Corrosion resistance classification CRC	4
Ambient temperature	-20 ... 80 °C
Torque at 6 bar	53.5 Nm
Spring return moment	20.5 Nm
Air consumption at 6 bar per cycle 0°-90°-0°	2.4 l
Product weight	2,200 g
Shaft connection	V14
Pneumatic connection	Sub-base G1/4
Materials note	Contains PWIS substances