



DRE-375-F14-Q12-FS

Semi-rotary drive

Feature	Data/description
Mode of operation	single-acting
Design structure	Rack and pinion
Ambient temperature	-20 - 80 °C
Pneumatic connection	Sub-base Female thread 1/4
Position detection	none
Cushioning	none
Rotation angle adjustment range	90,000 deg
Operating pressure	<= 10,000 bar
Product weight	96.200,000 g
Operating medium	Dried compressed air, lubricated or unlubricated
Corrosion resistance classification CRC	3
Size of actuator	375
Fitting connection conforms to standard	ISO 5211
Flange hole pattern	F14
Shaft connection	V36
Air consumption per cycle	17,00000 l
Efficiency of actuator	90,0 %
Valve connection conforms to standard	VDI/VDE 3845 (NAMUR)