

# Push-in L-fitting QSLF-1/4-1/4-U

Part number: 190730

FESTO

360° swivelling, internal thread with external hexagon.

This product is only available if ordered from the Festo Corporation, USA.

Products to be discontinued. Available until 2011.



## Data sheet

| Feature                                  | Value  |
|--|--|
| Size                                     | Standard                                       |
| Nominal size                             | 4.7 mm   |
| Assembly position                        | Any  |
| Container size                           | 1  |
| Design structure                         | Push/pull principle                            |
| Operating pressure                       | -0.95 ... 10 bar                               |
| Temperature dependent operating pressure | -0.95 ... 10 bar                               |
| Operating medium                         | Filtered compressed air<br>Vacuum              |
| Corrosion resistance classification CRC  | 1  |
| Ambient temperature                      | -10 ... 60 °C                                  |
| Authorisation                            | Germanischer Lloyd                             |
| Max. tightening torque                   | 14 Nm  |
| Product weight                           | 22 g   |
| Pneumatic connection                     | NPT1/4-18<br>for tubing, 1/4" outside diameter |
| Colour of release ring                   | Grey   |
| Materials note                           | Conforms to RoHS                               |
| Materials information, housing           | PBT  |
| Release ring material data               | POM  |
| Materials information for tubing seal    | NBR  |
| Hose clamping segment material data      | High alloy steel, non-corrosive                |