

CPE10SC-PRS-3

Connector block

Data sheet

Part no.: 192531

Page:1

| Feature | Data/description |
|-------------------------------------|--|
| Type sub-base/manifold | Manifold |
| Number valve ports | 3 |
| Distance between valve ports | 15,5 mm |
| Type of mounting sub-base | Through-hole |
| Type of mounting valve | Screw |
| Operating pressure min. | -0,9 bar |
| Operating pressure max. | 16 bar |
| Minimum ambient temperature | -10 °C |
| Maximum ambient temperature | 80 °C |
| Ducted main ports | 1+3+5 |
| Air connection type connection 1 | Thread |
| Air connection type connections 3,5 | Thread |
| Thread for port 1 | G 1/8 |
| Thread for ports 3, 5 | G 1/8 |
| Material of sub-base | Wrought aluminium alloy |
| Medium | Compressed air, vacuum (may also be lubricated) |