

CPE10SC-PRS-5

Connector block

Data sheet

Part no.: 192533

Page:1

Feature	Data/description
Type sub-base/manifold	Manifold
Number valve ports	5
Distance between valve ports	15,5 mm
Type of mounting sub-base	Through-hole
Type of mounting valve	Screw
Operating pressure min.	-0,9 bar
Operating pressure max.	16 bar
Minimum ambient temperature	-10 °C
Maximum ambient temperature	80 °C
Ducted main ports	1+3+5
Air connection type connection 1	Thread
Air connection type connections 3,5	Thread
Thread for port 1	G 1/8
Thread for ports 3, 5	G 1/8
Material of sub-base	Wrought aluminium alloy
Medium	Compressed air, vacuum (may also be lubricated)