

**CPE10SC-PRS-7**

Connector block

Data sheet

Part no.: 192535

Page:1

<b>Feature</b>	<b>Data/description</b>
Type sub-base/manifold	<b>Manifold</b>
Number valve ports	<b>7</b>
Distance between valve ports	<b>15,5 mm</b>
Type of mounting sub-base	<b>Through-hole</b>
Type of mounting valve	<b>Screw</b>
Operating pressure min.	<b>-0,9 bar</b>
Operating pressure max.	<b>16 bar</b>
Minimum ambient temperature	<b>-10 °C</b>
Maximum ambient temperature	<b>80 °C</b>
Ducted main ports	<b>1+3+5</b>
Air connection type connection 1	<b>Thread</b>
Air connection type connections 3,5	<b>Thread</b>
Thread for port 1	<b>G 1/8</b>
Thread for ports 3, 5	<b>G 1/8</b>
Material of sub-base	<b>Wrought aluminium alloy</b>
Medium	<b>Compressed air, vacuum (may also be lubricated)</b>