


Service unit FRC-1-D-7-O-MAXI

Part number: 192639

FESTO



Data sheet

Feature	Value
Size	Maxi
Series	D
Actuator lock	Rotary knob with detent
Mounting position	Vertical +/-5°
Condensate drain	Manually rotating
Design	Filter regulator without pressure gauge Proportional standard mist lubricator
Max. condensate volume	80 cm ³
Grade of filtration	40 µm
Bowl guard	Metal bowl guard
Pressure gauge (ANALOG) or Pressure display (DIGITAL)	Prepared for G1/4
Operating pressure	1 bar...16 bar
Pressure regulation range	0.5 bar...7 bar
Max. pressure hysteresis	0.4 bar
Standard nominal flow rate	8700 l/min
Operating medium	Compressed air to ISO 8573-1:2010 [-:::]
LABS (PWIS) conformity	VDMA24364-B1/B2-L
Media temperature	-10 °C...60 °C
Ambient temperature	-10 °C...60 °C
Product weight	2520 g
Type of mounting	In-line installation With accessories
Pneumatic connection, port 1	G1
Pneumatic connection, port 2	G1
Material housing	Die-cast zinc
Material bowl	PC