

Planar surface gantry EXCH-60-

Part number: 1939785

FESTO



Data sheet

Feature	Value
Size	60
Mounting position	Vertical Horizontal
Design	Planar surface gantry
Operating pressure	8 bar
Max. horizontal acceleration	50 m/s ²
Max. vertical acceleration	30 m/s ²
Max. horizontal speed	5 m/s
Max. vertical speed	3 m/s
Repetition accuracy	±0.1 mm
Duty cycle	100%
CE mark (see declaration of conformity)	To EC Machinery Directive
CE marking (see declaration of conformity)	To UK regulations for machines
LABS (PWIS) conformity	VDMA24364 zone III
Storage temperature	-10 °C...60 °C
Relative air humidity	0 - 90% Non-condensing
Sound pressure level	81 dB(A)
Degree of protection	IP40
Ambient temperature	10 °C...50 °C
Nominal load at max. dynamic response	6 kg
Type of mounting	Via mounting kit Via adjusting kit Via slot nuts
Note on materials	RoHS-compliant