

CPV18-EPR-PGU

End plate

Data sheet

Part no.: 194006

Page:1

Feature	Data/description
Air connection type	Sub-base
Operating pressure min.	0 bar
Operating pressure max.	10 bar
Minimum ambient temperature	-5 °C
Maximum ambient temperature	50 °C
Sound pressure level	85,4 dB(A)
Standard nominal flow rate	11000 l/min
Material of shock absorber insert	Sintered stainless steel