

Cartridge

QSP10-1/4-U


Part number: 194498
Product to be discontinued

FESTO

With push-in connector, straight

This product is only available if ordered from the Festo Corporation, USA.

Type to be discontinued. Available until 2017. See Support Portal for alternative products.



Data sheet

Feature	Value
Assembly position	Any
Container size	1
Design structure	Push/pull principle
Operating pressure complete temperature range	-0.95 ... 10 bar
Operating medium	Compressed air in accordance with ISO8573-1:2010 [7::-]
Note on operating and pilot medium	Lubricated operation possible
Corrosion resistance classification CRC	1
Ambient temperature	-5 ... 60 °C
Authorisation	Germanischer Lloyd
Pneumatic connection, port 1	QSP...10
Pneumatic connection, port 2	for tubing, 1/4" outside diameter
Colour of release ring	Grey
Materials note	Conforms to RoHS
Materials information, housing	Nickel plated Brass
Release ring material data	POM
Materials information for tubing seal	NBR
Hose clamping segment material data	High alloy steel, non-corrosive