


## FRCS-3/8-D-MIDI-KE-A

### Service unit combination

| Feature                      | Data/description   |
|------------------------------|--|
| Size                         | Midi   |
| Series                       | D  |
| Actuator lock                | Rotary knob with integrated lock   |
| Assembly position            | Vertical +/- 5°  |
| Grade of filtration          | 40 µm  |
| Condensate drain             | fully automatic  |
| Design structure             | On/off valve<br>Filter regulator with pressure gauge<br>Proportional standard oil-mist lubricator<br>Safety start-up valve |
| Max. condensate volume       | 43 cm <sup>3</sup>   |
| Bowl guard                   | Metal bowl guard   |
| Pressure gauge               | with pressure gauge  |
| Pressure control range       | 2,5 - 12 bar   |
| Inlet pressure 1             | 3,5 - 12 bar   |
| Max. pressure hysteresis     | 0,2 bar  |
| Standard nominal flow rate   | 1.420 l/min  |
| Operating medium             | Compressed air   |
| Medium temperature           | -10 - 60 °C  |
| Ambient temperature          | -10 - 60 °C  |
| Product weight               | 3.040 g  |
| Mounting type                | Optional<br>Line installation<br>with accessories  |
| Pneumatic connection, port 1 | G3/8   |
| Pneumatic connection, port 2 | G3/8   |



## FRCS-3/8-D-MIDI-KE-A

### Service unit combination

| Feature                        | Data/description         |
|--------------------------------|--------------------------|
| Materials note                 | Contains PWIS substances |
| Materials information, housing | Zinc die-casting         |
| Materials information for bowl | PC                       |