


manifold block MHA1-P10-2-M3

Part number: 197211

FESTO

for manifold block valves MHA1-...-HC/TC



Data sheet

Feature	Value
Max. number of valve positions	10
Operating pressure	0 ... 8 bar
Operating medium	Compressed air in accordance with ISO8573-1:2010 [7:4:4]
Note on operating and pilot medium	Lubricated operation possible (subsequently required for further operation)
Corrosion resistance classification CRC	1 - Low corrosion stress
PWIS conformity	VDMA24364-B2-L
Ambient temperature	-10 ... 60 °C
Mounting method for sub-base	with through hole
Mounting method for valve	with internal (female) thread
Pneumatic connection, port 1	M7
Pneumatic connection, port 2	M3
Material of connecting plate	Wrought Aluminium alloy