

Spiral plastic tubing PUN-6X1-S-6-BL

Part number: 197592

FESTO



Data sheet

Feature	Value
Working length	6 m
Outside diameter	6 mm
Block length	1.214 m
Inside diameter	4 mm
Winding diameter	46 mm
Number of turns	168
Temperature-dependent operating pressure	-0.95 bar...10 bar
Approval	German Technical Control Board (TÜV)
Certificate issuing authority	B 013277 0506 00
Operating medium	Compressed air to ISO 8573-1:2010 [7::-]
LABS (PWIS) conformity	VDMA24364-B2-L
Ambient temperature	-35 °C...60 °C
Product weight	350 g
Pneumatic connection	For push-in connector O.D. 6 mm For barbed fitting I.D. 4 mm with union nut For barbed fitting I.D. 4 mm
Colour	Blue
Shore hardness	D 52 +/-3
Material tubing	TPE-U(PU)