

Spiral plastic tubing PUN-12X2-S-6-BL

Part number: 197601

FESTO



Data sheet

| Feature | Value |
|--|---|
| Working length | 6 m |
| Outside diameter | 12 mm |
| Block length | 0.98 m |
| Inside diameter | 8 mm |
| Winding diameter | 95 mm |
| Number of turns | 64 |
| Temperature-dependent operating pressure | -0.95 bar...10 bar |
| Approval | German Technical Control Board (TÜV) |
| Certificate issuing authority | B 013277 0506 00 |
| Operating medium | Compressed air to ISO 8573-1:2010 [7::-] |
| LABS (PWIS) conformity | VDMA24364-B2-L |
| Ambient temperature | -35 °C...60 °C |
| Product weight | 1300 g |
| Pneumatic connection | For push-in connector outside diameter of 12 mm |
| Colour | Blue |
| Shore hardness | D 52 +/-3 |
| Material tubing | TPE-U(PU) |