

# DUO spiral plastic tubing PUN-10X1,5-S-2-DUO-BS

Part number: 197627

FESTO

Highly flexible, hydrolysis resistant to a great extent



## Data sheet

Feature	Value
Working length	2 m
Outside diameter	10 mm
Block length	0.66 m
Inside diameter	7 mm
Coil diameter	80 mm
Number of windings	22
Temperature dependent operating pressure	-0.95 ... 10 bar
Authorisation	TÜV
Certificate issuing department	B 013277 0506 00
Operating medium	Compressed air in accordance with ISO8573-1:2010 [7::-]
PWIS conformity	VDMA24364-B2-L
Ambient temperature	-35 ... 60 °C
Product weight	490 g
Pneumatic connection	For push-in connector outside diameter 10 mm
Colour	blue/black
Shore hardness	D 52 +/-3
Material tubing	TPE-U(PU)