

# Rotary distributor GF-3/8

Part number: 2095

FESTO



## Data sheet

Feature	Value
Nominal size	15 mm
Mounting position	optional
Operating pressure complete temperature range	-0.95 bar...10 bar
Max. rotational speed	300 rpm
Operating medium	Compressed air to ISO 8573-1:2010 [7::-]
Note on operating and pilot medium	Lubricated operation possible (in which case lubricated operation will always be required)
LABS (PWIS) conformity	VDMA24364-B1/B2-L
Media temperature	-10 °C...60 °C
Ambient temperature	-10 °C...60 °C
Pneumatic connection, port 1	Male thread G3/8
Pneumatic connection, port 2	Female thread G3/8
Note on materials	RoHS-compliant