

metal braided hose


P-6-BL

Part number: 2231

Product to be discontinued

FESTO

Type to be discontinued. Available until 2018. See Support Portal for alternative products.



Data sheet

Feature	Value
Outside diameter	13 mm
Bending radius relevant for flow rate	45 mm
Inside diameter	6 mm
Min. bending radius	20 mm
Operating pressure complete temperature range	-0.95 ... 16 bar
Operating medium	Compressed air in accordance with ISO8573-1:2010 [7:-:-]
Ambient temperature	-20 ... 80 °C
Product weight according to length	0.144 kg/m
Pneumatic connection	für Stecktülle Innen-Ø 6 mm
Colour	blue
Shore hardness	A 68 +/- 5
Materials note	Free of copper and PTFE Conforms to RoHS
Materials information for tubing	NBR