


power supply unit CACN-3A-1-5

Part number: 2247681

Product to be discontinued

FESTO

Type to be discontinued. Available until 2022. See Support Portal for alternative products.



Data sheet

Feature	Value
Width	40 mm
Height	130 mm
Length	115 mm
Assembly position	Free convection
Primary supply	Single-phase
Input current	0,9 - 1,65 A
Nominal output voltage DC	24 V
Nominal output current	5 A
Input voltage range AC	100 ... 240 V
Power failure buffering	110 ms
Line frequency	45 ... 65 Hz
Authorisation	C-Tick c UL us - Listed (OL)
CE mark (see declaration of conformity)	to EU directive for EMC to EU directive low-voltage devices
PWIS conformity	VDMA24364 zone III
Storage temperature	-40 ... 85 °C
Relative air humidity	95 %
Protection class	IP20
Ambient temperature	-25 ... 70 °C
Product weight	600 g
Mounting type	with top-hat rail
Materials note	Conforms to RoHS