

# Silencer U-1/4

Part number: 2316

FESTO



## Data sheet

Feature	Value
Mounting position	optional
Operating pressure	0 MPa...1 MPa 0 bar...10 bar
Flow rate to atmosphere	3300 l/min
Operating medium	Compressed air to ISO 8573-1:2010 [7:-:-]
Note on operating and pilot medium	Lubricated operation possible
LABS (PWIS) conformity	VDMA24364-B1/B2-L
Sound pressure level	76 dB(A)
Ambient temperature	-10 °C...70 °C
Product weight	7.7 g
Pneumatic connection	G1/4
Material shock absorber insert	PE
Note on materials	RoHS-compliant