


connecting cable NEDV-L2R1-V7-M12W3-K-0.1L1-N-M8W4-0.2R1

Part number: 2384165

FESTO



Data sheet

Feature	Value
Based on the standard	EN 61076-2-101 EN 61076-2-104 EN 61984
Assembly position	Any
Product weight	28 g
Electrical connection 1	2x angled sockets , M12, 3-pin
Electrical connection 2	Angled plug, M8, 4-pin
Operating voltage range DC	0 ... 30 V
Acceptable current load at 40°C	2 A
Cable length	0.2 m
Cable diameter	2.9 mm
Cable structure	2x0,14
Protection class	IP65
Ambient temperature	-25 ... 80 °C
PWIS conformity	VDMA24364-B1/B2-L
Materials note	Conforms to RoHS
Corrosion resistance classification CRC	2 - Moderate corrosion stress
Material cable sheath	TPE-U(PUR)