

# Clamping sleeve EAMH-86-19-C27.3-P

Part number: 2406019

FESTO



## Data sheet

| Feature                | Value                 |
|------------------------|-----------------------|
| Size                   | 86                    |
| Mounting position      | optional              |
| Max. rotational speed  | 5000 rpm              |
| LABS (PWIS) conformity | VDMA24364-B2-L        |
| Storage temperature    | -25 °C...60 °C        |
| Relative air humidity  | 0 - 95%               |
| Ambient temperature    | -10 °C...60 °C        |
| Mass moment of inertia | 7.1 kgmm <sup>2</sup> |
| Product weight         | 78 g                  |
| Note on materials      | RoHS-compliant        |