

# clamping sleeve EAMH-86-19-C27.3

Part number: 2429535

FESTO



## Data sheet

Feature	Value
Size	86
Assembly position	Any
Max. speed	5,000 1/min
PWIS conformity	VDMA24364-B2-L
Storage temperature	-25 ... 60 °C
Relative air humidity	0 - 95 %
Ambient temperature	-10 ... 60 °C
Mass moment of inertia	8.2 kgmm <sup>2</sup>
Product weight	76 g
Materials note	Conforms to RoHS