

# butterfly valve


## VZFB-D-65-WW-V4V4E

Part number: 2464102  
Product to be discontinued

FESTO

Nominal width DN65, with welded ends, DIN 11850, EPDM, material 1.4404.

Type to be discontinued. Available until 2022. See Support Portal for alternative products.



### Data sheet

Feature	Value
Design structure	2-way disc valve
Type of actuation	manual
Sealing principle	soft
Assembly position	Any
Mounting type	Line installation
Process valve connection	Weld-on ends/weld-on ends
Nominal diameter DN	65
Flow direction	reversible
Nominal pressure of process valve	10
Actuation torque	18 Nm
Based on the standard	DIN 11851
Medium	Water Neutral fluids
Medium temperature	-10 ... 120 °C
Materials note	Contains PWIS substances Conforms to RoHS
Food-safe	See Supplementary material information
Material housing	High alloy steel, non-corrosive
Material number for housing	1.4404
Material disc	High alloy steel, non-corrosive
Material number for disc	1.4404
Material shaft	High alloy steel, non-corrosive
Material number for shaft	1.4404
Product weight	2,100 g
Corrosion resistance classification CRC	4 - Very high corrosion stress