

butterfly valve

VZFB-D-100-WW-V2V2E

Part number: 2466755
Product to be discontinued

FESTO

Nominal width DN100, with welded ends, DIN 11850, EPDM, material 1.4301.

Type to be discontinued. Available until 2022. See Support Portal for alternative products.



Data sheet

| Feature | Value |
|---|--|
| Design structure | 2-way disc valve |
| Type of actuation | manual |
| Sealing principle | soft |
| Assembly position | Any |
| Mounting type | Line installation |
| Process valve connection | Weld-on ends/weld-on ends |
| Nominal diameter DN | 100 |
| Flow direction | reversible |
| Nominal pressure of process valve | 10 |
| Actuation torque | 35 Nm |
| Based on the standard | DIN 11851 |
| Medium | Water Neutral fluids |
| Medium temperature | -10 ... 120 °C |
| Materials note | Contains PWIS substances Conforms to RoHS |
| Food-safe | See Supplementary material information |
| Material housing | High alloy steel, non-corrosive |
| Material number for housing | 1.4301 |
| Material disc | High alloy steel, non-corrosive |
| Material number for disc | 1.4301 |
| Material shaft | High alloy steel, non-corrosive |
| Material number for shaft | 1.4301 |
| Product weight | 3,100 g |
| Corrosion resistance classification CRC | 3 - High corrosion stress |