


# butterfly valve

## VZFB-SZ-11/2"-TT-V4V4V

Part number: 2468959  
 Product to be discontinued

FESTO

Nominal width 1 1/2", with thread, SMS 1145, FPM, material 1.4404.  
 Type to be discontinued. Available until 2022. See Support Portal for alternative products.



### Data sheet

Feature	Value
Design structure	2-way disc valve
Type of actuation	manual
Sealing principle	soft
Assembly position	Any
Mounting type	Line installation
Process valve connection	Male thread/male thread
Nominal diameter DN	1 1/2"
Flow direction	reversible
Nominal pressure of process valve	10
Actuation torque	10 Nm
Based on the standard	SMS 1145
Medium	Water Neutral fluids
Medium temperature	-15 ... 140 °C
Materials note	Contains PWIS substances Conforms to RoHS
Food-safe	See Supplementary material information
Material housing	High alloy steel, non-corrosive
Material number for housing	1.4404
Material disc	High alloy steel, non-corrosive
Material number for disc	1.4404
Material shaft	High alloy steel, non-corrosive
Material number for shaft	1.4404
Product weight	1,500 g
Corrosion resistance classification CRC	4 - Very high corrosion stress