

Union nut MCK-PK-6

Part number: 2966

FESTO



Data sheet

| Feature | Value |
|---|--|
| Size | Female thread M12x1 |
| Operating pressure complete temperature range | 0 MPa...1 MPa 0 bar...10 bar 0 psi...145 psi |
| Corrosion resistance class CRC | 2 - Moderate corrosion stress |
| LABS (PWIS) conformity | VDMA24364-B2-L |
| Ambient temperature | -10 °C...60 °C |
| Pneumatic connection, port 1 | For tubing outer diameter of 8 mm For barbed fitting I.D. 6 mm with union nut |
| Material union nut | Wrought aluminium alloy, anodised |
| Note on materials | RoHS-compliant |