



## JMYH-5/2-2,3-LED-P

### Solenoid valve

Feature	Data/description
Nominal size	2,3 mm
Type of actuation	electrical
Sealing principle	soft
Manual override	resetting
Design structure	Piston slide
Type of piloting	Piloted
Flow direction	non reversible
Valve function	5/2 Bistable
Standard nominal flow rate	190 l/min
Operating pressure	2 - 7 bar
Operating medium	Filtered, unlubricated compressed air, 5 µm filtration Filtered, lubricated compressed air, 5 µm filtration
Medium temperature	5 - 50 °C
Pilot medium	Filtered, unlubricated compressed air, 5 µm filtration Filtered, lubricated compressed air, 5 µm filtration
Ambient temperature	5 - 50 °C
Mounting type	with through hole
Pneumatic connection, port 1	Sub-base
Pneumatic connection, port 2	Sub-base
Pneumatic connection, port 3	Sub-base
Pneumatic connection, port 4	Sub-base
Pneumatic connection, port 5	Sub-base