

Protective conduit MKG-36-PG-29

Part number: 3156319

FESTO



Data sheet

Feature	Value
Mounting position	optional
Corrosion resistance class CRC	2 - Moderate corrosion stress
LABS (PWIS) conformity	VDMA24364-B2-L
Ambient temperature	-20 °C...100 °C
Note on materials	RoHS-compliant
Material conduit	PP