

# clevis foot LBG-80

Part number: 31765

FESTO

for spherical bearing with swivel flange SSNG or rod eye SGS and cylinders DNGU, DNG, DNC.  
or for spherical bearing with swivel flange SNCS or rod eye SGS with cylinders AEN, ADN, ADNP.



## Data sheet

Feature	Value
Size	80
Corrosion resistance classification CRC	2 - Moderate corrosion stress
PWIS conformity	VDMA24364-B2-L
RSBP classification to CD-0033	F5
Ambient temperature	-40 ... 150 °C
Product weight	1,050 g
Materials note	Conforms to RoHS
Material mounting	Nodular graphite cast iron
Material mounting pin	Case-hardened steel
Material lock	Spring steel