

Right angle clevis foot LQG-125

Part number: 31774

FESTO



Data sheet

Feature	Value
Size	125
Corrosion resistance class CRC	1 - Low corrosion stress
LABS (PWIS) conformity	VDMA24364-B1/B2-L
Ambient temperature	-40 °C...150 °C
Product weight	3778 g
Note on materials	RoHS-compliant
Material mounting	Spheroidal graphite cast iron
Material bolt	Case-hardened steel
Material lock	Spring steel