

# Valve VOFD-L50T-

Part number: 3212962

FESTO



## Data sheet

Feature	Value
Valve function	3/2-way, closed, monostable
Type of actuation	Electric
Construction width	28 mm 50.5 mm 51 mm
Standard nominal flow rate	493 l/min
pneumatic working port	Flange 1/4 G1/4 1/4 NPT NAMUR port pattern
Operating pressure	0 MPa...1 MPa 0 bar...10 bar
Design	Directly actuated poppet valve
Type of reset	Mechanical spring
Degree of protection	IP65
Certificate issuing authority	TÜV 968/V 1251.00/21
Nominal size	5 mm
Sealing principle	Soft
Mounting position	optional
Manual override	None
Type of piloting	Direct
Flow direction	Reversible
Suitability for vacuum	yes
b value	0.25
C value	2 l/sbar
Flow rate Kv pressurisation	0.36 m <sup>3</sup> /h
Flow rate Kv exhaust	0.36 m <sup>3</sup> /h
Standard nominal flow rate 2-3	429 l/min
Switching time off	60 ms
Switching time on	40 ms
Explosion protection	Zone 1 (ATEX) Zone 2 (ATEX) Zone 21 (ATEX) Zone 22 (ATEX)

<b>Feature</b>	<b>Value</b>
Operating medium	Compressed air to ISO 8573-1:2010 [7:2:2]
Extended ambient temperature	-25 ... 60° C Low demand mode
Corrosion resistance class CRC	4 - Very high corrosion stress
LABS (PWIS) conformity	VDMA24364 zone III
Media temperature	-25 °C...60 °C
Ambient temperature	-25 °C...60 °C
Product weight	560 g
Note on materials	RoHS-compliant
Material seals	NBR
Material housing	Ematal coated aluminium High-alloy stainless steel