

HE-1/4-S-B

Soft-start valve

Data sheet

Part no.: 33017

Page:1

| Feature | Data/description |
|----------------------------------|---|
| Switching function | 3/2-way valve, normally closed |
| Switching function short code | 3/2 |
| Direction of flow reversible | No |
| Operating principle | Slide |
| Shape of function component | Sub-base |
| With exhaust flow control | No |
| Type of regulation | Direct |
| Control type | Bistable |
| Type of mounting | Screw + line |
| Installation position | Any |
| Nominal size | 11,3 mm |
| Operating pressure min. | 1 bar |
| Operating pressure max. | 14 bar |
| Minimum ambient temperature | -10 °C |
| Maximum ambient temperature | 60 °C |
| Minimum medium temperature | -10 °C |
| Maximum medium temperature | 60 °C |
| Type of connection, air supply | Thread |
| Connecting thread, supply port | G 1/4 |
| Air connection type power port | Thread |
| Connecting thread, working port | G 1/4 |
| Type of connection, exhaust | Thread |
| Connecting thread, exhaust port | G 1/4 |
| Actuation/reset | Lever, detenting |
| Standard nominal flow rate 1 - 2 | 2100 l/min |
| Standard nominal flow rate 2 - 3 | 120 l/min |
| Medium | Compressed air, filtered 50 µm (may be lubricated) |