


Foot mounting DAMH-Q12-12

Part number: 3371842

FESTO



Data sheet

Feature	Value
Size	12
Mounting position	optional
Corrosion resistance class CRC	1 - Low corrosion stress
LABS (PWIS) conformity	VDMA24364-B2-L
Ambient temperature	0 °C...60 °C
Max. tightening torque	2.4 Nm
Product weight	79 g
Type of mounting	With through-hole
Note on materials	RoHS-compliant
Material bracket	Galvanised steel