


Clevis foot LBZS-40

Part number: 33844

FESTO



Data sheet

Feature	Value
Size	40
Mounting position	optional
Corrosion resistance class CRC	2 - Moderate corrosion stress
LABS (PWIS) conformity	VDMA24364-B2-L
Ambient temperature	-40 °C...150 °C
Product weight	138 g
Note on materials	RoHS-compliant
Material mounting	Stainless steel casting