

Solenoid coil MSFG-42-OD

Part number: 34413

FESTO



Data sheet

Feature	Value
Mounting position	optional
Switching position indicator	no
Min. pick-up time	10 ms
Duty cycle	100%
Characteristic coil data	42 V DC: 5.5 W
Permissible voltage fluctuations	+/- 10 %
LABS (PWIS) conformity	VDMA24364-C1-L
Degree of protection	IP65
Ambient temperature	-5 °C...40 °C
Max. tightening torque for socket	0.4 Nm
Product weight	55 g
Electrical connection	3-pin Plug pins with connection pattern to Festo standard for MSSD-F
Type of mounting	Via knurled nut
Note on materials	RoHS-compliant
Material solenoid coil	Duroplast Copper Steel
Material winding	Copper