

# Plastic tubing

## PL-3-BL

Part number: 3453

FESTO

For CK and N connectors (approved for use in the food processing industry).

The maximum pressure value is permissible at the maximum temperature.



### Data sheet

Feature	Value
Outside diameter	4.3 mm
Bending radius relevant for flow rate	18 mm
Inside diameter	3 mm
Temperature dependent operating pressure	-0.95 ... 9 bar
Operating medium	Compressed air in accordance with ISO8573-1:2010 [7::-:]
Ambient temperature	-30 ... 60 °C
Authorisation	TÜV
Product weight according to length	0.0068 kg/m
Colour	blue
Shore hardness	D 42 +/-3
Materials note	Free of copper and PTFE Conforms to RoHS
Materials information for tubing	PE