


Guide unit FENG-100-500-KF

Part number: 34536

FESTO



Data sheet

Feature	Value
Size	100
Stroke	500 mm
Mounting position	optional
Guide	Recirculating ball bearing guide
Design	Guidance
Explosion protection	Zone 1 (ATEX) Zone 2 (ATEX) Zone 21 (ATEX) Zone 22 (ATEX)
LABS (PWIS) conformity	VDMA24364-B2-L
Ambient temperature	-20 °C...80 °C
Max. force F _y	2300 N
Max. force F _y static	3120 N
Max. force F _z	2300 N
Max. force F _z static	3120 N
Max. moment M _x	198 Nm
Max. torque M _x static	268 Nm
Max. moment M _y	197 Nm
Max. torque M _y static	267 Nm
Max. moment M _z	197 Nm
Max. torque M _z static	267 Nm
Displacement force	40 N
Product weight	16840 g
Type of mounting	Via female thread
Note on materials	RoHS-compliant
Material guide component	Tempered steel
Material housing	Anodised wrought aluminium alloy
Material yoke plate	Tempered steel