

time delay valve



VZOA-3-1/4

Part number: 3464

Classic - do not use for new projects

Modern alternatives can be found by entering the first four characters of the type code in the search field.

FESTO



Data sheet

Feature	Value
Operating pressure MPa	0 ... 1 MPa
Operating pressure	0 ... 10 bar
Standard nominal flow rate	600 l/min
Adjustable delay times	0 ... 30 s
Operating medium	Compressed air in accordance with ISO8573-1:2010 [7:-:-]
Note on operating and pilot medium	Lubricated operation possible (subsequently required for further operation)
PWIS conformity	VDMA24364-B2-L
Mounting type	with through hole
Pneumatic connection	G1/8 G1/4
Materials note	Conforms to RoHS