

# Illuminating seal MV-LD-12-24DC

Part number: 35558

FESTO



## Data sheet

Feature	Value
Switching position indicator	LED
Type of mounting	On solenoid valve via M3 central screw
Product weight	1.6 g
Electrical connection	Type B To DIN EN 175301-803 Square design MSV
Operational voltage range DC	12 V...24 V
Protective conductor connection	Available
Nominal power illuminating seal	0.05 W
Degree of protection	IP65
Ambient temperature	-25 °C...85 °C
LABS (PWIS) conformity	VDMA24364-B2-L
Material housing	TPE-U(PU)
Colour	Transparent