



Intermediate pressure regulator plate LR-ZP-A-D-2

Part number: 35970
Product to be discontinued

For ISO valves.

Type to be discontinued. Available until 2018. See Support Portal for alternative products.

FESTO



Data sheet

Feature	Value
Based on the standard	ISO 5599-1
Integrated function	Pressure regulator
Design structure	Piston
Pressure regulation range	0.5 ... 12 bar
Inlet pressure 1	≤ 14 bar
Authorisation	UL - Recognized (OL)
Product weight	960 g
Materials note	Contains PWIS substances
Materials information for seals	NBR
Materials information, housing	Aluminium die cast Steel