

# Plastic tubing

## PL-13-BL

Part number: 4103

FESTO

For CK and N connectors.

The maximum pressure value is permissible at the maximum temperature.



## Data sheet

Feature	Value
Outside diameter	17.6 mm
Bending radius relevant for flow rate	100 mm
Inside diameter	13 mm
Temperature dependent operating pressure	0 ... 7 bar
Operating medium	Compressed air in accordance with ISO8573-1:2010 [7:-:-]
Ambient temperature	-10 ... 35 °C
Product weight according to length	0.135 kg/m
Colour	blue
Shore hardness	A 85 +/-3
Materials note	Free of copper and PTFE Conforms to RoHS
Materials information for tubing	PVC-P